


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)" (see www.standard1288.org or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 3, 15.08.2015, SN 0001(Baumer), recalibrated 28.08.2017. The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by Technical and Application Support Center, Baumer Optronik GmbH.



Vendor	Baumer
Model	VEXG-100C.R
Serial number	700003540565
Sensor diagonal	7.92 mm
Lens category	CS-Mount
Resolution	3856 × 2764, 12 bit
Pixel size	1.67 μm × 1.67 μm
Sensor	Micron MT9J003
Sensor type	CMOS
Shutter type	Rolling shutter
Overlap capabilities	Overlapped
Maximum frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	465.2 nm
Wavelength FWHM	20.8 nm
Gain / BlackLevel	1.0 / 36.0
Operation point 2	
Wavelength centroid	535.8 nm
Wavelength FWHM	31.9 nm
Gain / BlackLevel	1.0 / 36.0
Operation point 3	
Wavelength centroid	630.8 nm
Wavelength FWHM	13.3 nm
Gain / BlackLevel	1.0 / 36.0
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain / BlackLevel	1.0 / 36.0
Exposure control	By irradiance	Environmental temperature	25.5°C
Exposure time	3.17 ms	Camera body temperature	31.1°C
Frame rate	0.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	465 nm, 20.8 nm



Quantum efficiency

η 39.8%

Overall system gain

K 0.692 DN/e⁻

1/ K 1.445 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 3.35 DN

DSNU₁₂₈₈ 0.40 DN

σ_d 4.83 e⁻

DSNU₁₂₈₈ 0.58 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 71

37.1 dB

6.2 bit

1/SNR_{max} 1.40 %

PRNU₁₂₈₈ 1.00 %

Nonlinearity

LE 0.20%

LE_{min} -0.22%

LE_{max} 0.18%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 13.48 p

4.833 p/ μm^2

$\mu_{p,\text{sat}}$ 12729 p

4564 p/ μm^2

$\mu_{e,\text{min}}$ 5.37 e⁻

1.926 e⁻/ μm^2

$\mu_{e,\text{sat}}$ 5072 e⁻

1819 e⁻/ μm^2

Dynamic range

DR 944

59.5 dB

9.9 bit

Dark current



$\mu_{c,\text{mean}}$ 0.0 DN/s

$\mu_{c,\text{mean}}$ 0.0 e⁻/s

$\mu_{c,\text{var}}$ -0.0 e⁻/s

EMVA 1288 Summary Sheet for Operating Point 2

Type of data	Single	Gain / BlackLevel	1.0 / 36.0
Exposure control	By irradiance	Environmental temperature	25.5°C
Exposure time	3.17 ms	Camera body temperature	31.1°C
Frame rate	0.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	536 nm, 31.9 nm



Quantum efficiency

η 31.1%

Overall system gain

K 0.716 DN/e⁻

1/ K 1.396 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 3.31 DN

DSNU₁₂₈₈ 0.43 DN

σ_d 4.60 e⁻

DSNU₁₂₈₈ 0.60 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 72

37.2 dB

6.2 bit

1/SNR_{max} 1.38 %

PRNU₁₂₈₈ 0.97 %

Nonlinearity

LE 0.34%

LE_{min} -0.29%

LE_{max} 0.38%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 16.51 p

5.918 p/ μm^2

$\mu_{p,\text{sat}}$ 16781 p

6017 p/ μm^2

$\mu_{e,\text{min}}$ 5.14 e⁻

1.844 e⁻/ μm^2

$\mu_{e,\text{sat}}$ 5227 e⁻

1874 e⁻/ μm^2

Dynamic range

DR 1017

60.1 dB

10.0 bit

Dark current



$\mu_{c,\text{mean}}$ 0.1 DN/s

$\mu_{c,\text{mean}}$ 0.1 e⁻/s

$\mu_{c,\text{var}}$ 0.2 e⁻/s

EMVA 1288 Summary Sheet for Operating Point 3

Type of data	Single	Gain / BlackLevel	1.0 / 36.0
Exposure control	By irradiance	Environmental temperature	25.5°C
Exposure time	3.17 ms	Camera body temperature	31.1°C
Frame rate	0.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	631 nm, 13.3 nm



Quantum efficiency

η 20.8%

Overall system gain

K 0.728 DN/e⁻

1/ K 1.373 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 3.35 DN

DSNU₁₂₈₈ 0.42 DN

σ_d 4.58 e⁻

DSNU₁₂₈₈ 0.58 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 69

36.8 dB

6.1 bit

1/SNR_{max} 1.44 %

PRNU₁₂₈₈ 1.70 %

Nonlinearity

LE 0.32%

LE_{min} -0.35%

LE_{max} 0.29%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 24.70 p

8.858 p/μm²

$\mu_{p,\text{sat}}$ 23205 p

8320 p/μm²

$\mu_{e,\text{min}}$ 5.13 e⁻

1.839 e⁻/μm²

$\mu_{e,\text{sat}}$ 4817 e⁻

1727 e⁻/μm²

Dynamic range

DR 939

59.5 dB

9.9 bit

Dark current

$\mu_{c,\text{mean}}$ 0.1 DN/s

$\mu_{c,\text{mean}}$ 0.1 e⁻/s

$\mu_{c,\text{var}}$ 0.1 e⁻/s