

DST53-Z250I

Performance strain sensor with current output

Article number: 11706116

Overview

- Measuring range 0 ... 250 $\mu\text{m/m}$
- 1:1 replacement for former DSRT 22DB-S5-0250/T - Art.: 10161828
- Cost-effective force measurement of large forces
- Minimal influence on the machine structure due to low stiffness
- Integrated amplifier electronics, output signal 4...20 mA
- Bore hole distance 53 mm
- M12 connector, 5 pin



Technical data

General data

Nominal strain	0 ... 250 $\mu\text{m/m}$
Non-linearity	< 0.5 %
Repeatability	< 0.1 %
Mechanical mounting	4 x M6 screws

Mechanical data

Overload	150 %
Fatigue strength	>10 Mio cycles at 0...100% FS
Sensor stiffness	260 N @ 250 $\mu\text{m/m}$
Weight	135 g
Material sensor body	1.7225, chemically nickel plated
Material housing	Stainless steel, 1.4301
Compensated for thermal expansion coefficient	$11.1 \cdot 10^{-6} \text{ 1/K}$
Electrical connection	M12, 5 pin, male

Environmental conditions

Operating temperature range	0 °C ... 70 °C
Storage temperature range	-40 °C ... 85 °C
Protection class EN 60529, ISO20653	IP 65

Environmental conditions

Vibration IEC 60068-2-6	10 ... 57 Hz: 1.5 mm p-p, 58 ... 2000 Hz: 10 g
Random IEC 60068-2-64	20 ... 1000 Hz: 0.1 g^2/Hz
Shock IEC 60068-2-27	50 g / 11 ms, 100 g / 6 ms


Electrical data

Output signal	4 ... 20 mA
Signal polarity positive	Tension
Bridge resistance	350 Ω
Supply voltage	18 ... 30 VDC
Current consumption	< 40 mA
Reverse polarity protection	Yes
Short circuit protection	Yes
Cut-off frequency (3 db)	1000 Hz
Zero adjustment active	$\geq 5 \text{ VDC}$
Zero adjustment inactive	$\leq 1 \text{ VDC}$
Zero adjustment time	< 30 ms

Compliance and approvals

Conformity	CE UL
------------	----------

Dimensional drawings (mm)



DST53-Z250I

Performance strain sensor with current output

Article number: 11706116

Electrical connection

Pin-number	Signals
1	+V _S
2	n. c.
3	GND
4	I _{OUT}
5	Tare
Case	Shield

