

GIM140R - 1-dimensional, analog

1-dimensional, measuring range 0...360°

Analog

Overview

- Size 48 mm
- Interface Analog
- MEMS capacitive measuring principle
- Measuring range 1-dimensional: 0...360°
- Aluminium housing
- Protection IP 67/IP 69K
- Connection cable
- Teach input for adjustment of zero position



Technical data

Technical data - electrical ratings

Voltage supply	8...30 VDC 12...30 VDC
Reverse polarity protection	Yes
Short-circuit proof	Yes
Consumption typ.	8 mA (24 VDC, w/o load, voltage output) 12 mA (w/o load, current output)
Interface	Analog (4...20 mA / 0.5...4.5 V / 0...10 V)
Load resistor	Between Out/0 V ≥ 3 k Ω / voltage output 270 Ω at 10 VDC (500 Ω at 15 VDC) / current output
Measuring range	0...30°, 0...60°, 0...90°, 0...120°, 0...180°, 0...270°, 0...360°
Resolution	0.2 °
Accuracy (+25 °C)	± 0.4 °
Sensing method	MEMS technology
Interference immunity	EN 61000-6-2

Technical data - electrical ratings

Emitted interference	EN 61000-6-3
Programmable parameters	Preset
Diagnostic function	Out-of-range diagnostics
Technical data - mechanical design	
Dimensions W x H x L	48 x 14 x 45 mm
Protection EN 60529	IP 67/IP 69K
Material	Housing: aluminium, anodised
Corrosion protection	ISO 9227:2017 salt mist according to ISO 12944-6:1998 C5-M (CX)
Operating temperature	-40...+85 °C
Resistance	EN 60068-2-6 Vibration 10 g, 10-2000 Hz EN 60068-2-27 Shock 50 g, 11 ms
Weight approx.	50 g
Connection	Cable 0.3 m, radial

Optional


- Analog output with out-of-range diagnostic

GIM140R - 1-dimensional, analog

1-dimensional, measuring range 0...360°





Analog

Installation position



The 1-dimensional inclination sensor must be installed with its x-axis in line with the force of gravity, as illustrated below.

The 1-dimensional sensor default position is 0° as shown in the following illustration.



Terminal assignment

Cable

Core color	Signal	Description
White	0 V	Ground relating to +Vs
Brown	+Vs	Voltage supply
Green	Out	Output
Yellow	n.c.	Do not use
Grey	Teach	Teach-input

Cable data: 5 x 0.5 mm²

GIM140R - 1-dimensional, analog



1-dimensional, measuring range 0...360°

Analog

Output signals

Analog output



Measuring range 0...90°



Output signals



Analog output

Measuring range 0...270°



Analog output

Measuring range 0...180°



GIM140R - 1-dimensional, analog



1-dimensional, measuring range 0...360°

Analog

Output signals

Analog output with out-of-range diagnostic



Measuring range 0...90°



Output signals



Analog output with out-of-range diagnostic

Measuring range 0...270°



Analog output with out-of-range diagnostic

Measuring range 0...180°



Trigger level

Teach-input

High level	>2.1 V
Low level	<1 V
Maximum	+Vs

Teach process

The teach-in function enables rapid and easy commissioning in the field.

Setting zero


- Get inclination sensor on position intended for zero position.
- Set teach input for 5 < t < 10 seconds on high level.

GIM140R - 1-dimensional, analog

1-dimensional, measuring range 0...360°

Analog

Dimensions



GIM140R - 1-dimensional, analog

1-dimensional, measuring range 0...360°

Analog

Ordering reference

GIM140R - M 1 ### . K ## . A #####

Product

GIM140R

Housing

Metal

M

Number of axes

1-dimensional

1

Measuring range

0...30°

030

0...60°

060

0...90°

090

0...120°

120

0...180°

180

0...270°

270

0...360°

360

Connection

 Cable 0.3 m, Standard 5x0.5 mm²

K

Voltage supply / interface

8...30 VDC / Analog 0.5...4.5 VDC

V3

12...30 VDC / Analog 0...10 VDC

V6

12...30 VDC / Analog 4...20 mA

C0

Operating temperature

-40...+85 °C

A

Option

Without option

Output signal with out-of-range diagnostics (Analog)

/4822

Accessories

Programming accessories

11084376

ZTEST-ALL.ANALOG