

| Product | Shaft | Pulses per revolution, output | Connection | Material number |
|---------|--------------------------------|---|---------------------|-----------------|
| HOG840 | Solid shaft ø11 mm | 1024, HTL-P | 1 x cable gland M20 | EHO840-11730613 |
| | | 2048, HTL-P | 1 x cable gland M20 | EHO840-11730659 |
| | | Parameterization at factory ¹⁾ | 1 x cable gland M20 | EHO840-11730660 |
| | Blind hollow shaft ø12G7 mm | 1024, HTL-P | 1 x cable gland M20 | EHO840-11730661 |
| | | 2048, HTL-P | 1 x cable gland M20 | EHO840-11730662 |
| | | Parameterization at factory ¹⁾ | 1 x cable gland M20 | EHO840-11730663 |
| | Blind hollow shaft ø16G7 mm | 1024, HTL-P | 1 x cable gland M20 | EHO840-11730664 |
| | | 2048, HTL-P | 1 x cable gland M20 | EHO840-11730665 |
| | | Parameterization at factory ¹⁾ | 1 x cable gland M20 | EHO840-11730666 |

1) Please choose resolution, output stage and zero pulse (length and position) with your order

Resolution: 1...32768 ppr

Output stage: HTL-P or TTL

Zero pulse:

- 90°, K1=K2=1

- 180°, K1=0

- 180°, K2=0

- 180°, K1=1

Example for EHO840 - 11730660: 5000 ppr, TTL, 180°, K2=0