


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for “Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)” (see www.standard1288.org or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 3, 15.08.2015, SN 0001(Baumer), recalibrated 28.08.2017 . The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.



Vendor	Baumer
Model	VLXT-50M.FO
Serial number	700004536439
Sensor diagonal	11.01 mm
Lens category	C-Mount
Resolution	2448 × 2048, 12 bit
Pixel size	3.45 μm × 3.45 μm
Sensor	Sony IMX250
Sensor type	CMOS
Shutter type	Global shutter
Overlap capabilities	Overlapped
Maximum frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	535.8 nm
Wavelength FWHM	31.9 nm
Gain / BlackLevel	1.0 / 39.0
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain / BlackLevel	1.0 / 39.0
Exposure control	By irradiance	Environmental temperature	23.6°C
Exposure time	1.58 ms	Camera body temperature	33.7°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono12	Wavelength, centr., FWHM	536 nm, 31.9 nm



Quantum efficiency

η 64.2%

Overall system gain

K 0.415 DN/e⁻

1/ K 2.410 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 0.91 DN

DSNU₁₂₈₈ 0.28 DN

σ_d 2.09 e⁻

DSNU₁₂₈₈ 0.67 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 97

39.7 dB

6.6 bit

1/SNR_{max} 1.03 %

PRNU₁₂₈₈ 0.55 %

Nonlinearity

LE 0.12%

LE_{min} -0.11%

LE_{max} 0.13%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 4.30 p

0.361 p/ μm^2

$\mu_{p,\text{sat}}$ 14657 p

1231 p/ μm^2

$\mu_{e,\text{min}}$ 2.76 e⁻

0.232 e⁻/ μm^2

$\mu_{e,\text{sat}}$ 9408 e⁻

790 e⁻/ μm^2

Dynamic range

DR 3410

70.7 dB

11.7 bit

Dark current

$\mu_{c,\text{mean}}$ -0.4 DN/s

$\mu_{c,\text{mean}}$ -0.9 e⁻/s

$\mu_{c,\text{var}}$ 0.4 e⁻/s