


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)" (see www.standard1288.org or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 3, 15.08.2015, SN 0001(Baumer) . The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by Technical and Application Support Center, Baumer Optronik GmbH.



Vendor	Baumer
Model	LXG-200C
Serial number	0738654515
Sensor diagonal	34.33 mm
Lens category	F-Mount
Resolution	4288 × 3224, 12 bit
Pixel size	6.40 μm × 6.40 μm
Sensor	CMOSIS CMV20000
Sensor type	CMOS
Shutter type	Global shutter
Overlap capabilities	Overlapped
Maximum frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	465.3 nm
Wavelength FWHM	20.7 nm
Gain / BlackLevel	1.0 / 44
Operation point 2	
Wavelength centroid	535.8 nm
Wavelength FWHM	32.0 nm
Gain / BlackLevel	1.0 / 44
Operation point 3	
Wavelength centroid	631.0 nm
Wavelength FWHM	13.4 nm
Gain / BlackLevel	1.0 / 44
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain / BlackLevel	1.0 / 44
Exposure control	By irradiance	Environmental temperature	25.3°C
Exposure time	486.00 μ s	Camera body temperature	35.0°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	465 nm, 20.7 nm



Quantum efficiency

η 41.5%

Overall system gain

K 0.337 DN/e⁻
 $1/K$ 2.966 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 2.53 DN
 DSNU_{1288} 5.09 DN
 σ_d 7.46 e⁻
 DSNU_{1288} 15.09 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 107
 40.6 dB
 6.7 bit
 $1/\text{SNR}_{\text{max}}$ 0.93 %
 PRNU_{1288} 1.56 %

Nonlinearity

LE 0.28%
 LE_{min} -0.20%
 LE_{max} 0.35%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 19.33 p
 0.472 p/ μm^2
 $\mu_{p,\text{sat}}$ 27611 p
 674 p/ μm^2
 $\mu_{e,\text{min}}$ 8.03 e⁻
 0.196 e⁻/ μm^2
 $\mu_{e,\text{sat}}$ 11461 e⁻
 280 e⁻/ μm^2

Dynamic range



DR 1428
 63.1 dB
 10.5 bit

Dark current

$\mu_{c,\text{mean}}$ 101.0 DN/s
 $\mu_{c,\text{mean}}$ 299.6 e⁻/s
 $\mu_{c,\text{var}}$ 132.2 e⁻/s

EMVA 1288 Summary Sheet for Operating Point 2

Type of data	Single	Gain / BlackLevel	1.0 / 44
Exposure control	By irradiance	Environmental temperature	25.3°C
Exposure time	486.00 μ s	Camera body temperature	35.0°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	536 nm, 32.0 nm



Quantum efficiency

η 46.6%

Overall system gain

K 0.304 DN/e⁻
 $1/K$ 3.295 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 2.53 DN
 DSNU_{1288} 4.00 DN
 σ_d 8.30 e⁻
 DSNU_{1288} 13.17 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 112
 41.0 dB
 6.8 bit
 $1/\text{SNR}_{\text{max}}$ 0.90 %
 PRNU_{1288} 1.73 %

Nonlinearity

LE 0.23%
 LE_{min} -0.19%
 LE_{max} 0.27%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 19.04 p
 0.465 p/ μm^2
 $\mu_{p,\text{sat}}$ 26812 p
 655 p/ μm^2
 $\mu_{e,\text{min}}$ 8.86 e⁻
 0.216 e⁻/ μm^2
 $\mu_{e,\text{sat}}$ 12483 e⁻
 305 e⁻/ μm^2

Dynamic range



DR 1408
 63.0 dB
 10.5 bit

Dark current

$\mu_{c,\text{mean}}$ 101.2 DN/s
 $\mu_{c,\text{mean}}$ 333.3 e⁻/s
 $\mu_{c,\text{var}}$ 165.0 e⁻/s

EMVA 1288 Summary Sheet for Operating Point 3

Type of data	Single	Gain / BlackLevel	1.0 / 44
Exposure control	By irradiance	Environmental temperature	25.3°C
Exposure time	486.00 μ s	Camera body temperature	35.0°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	631 nm, 13.4 nm



Quantum efficiency

η 41.6%

Overall system gain

K 0.335 DN/e⁻

1/ K 2.981 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 2.50 DN

DSNU₁₂₈₈ 3.50 DN

σ_d 7.40 e⁻

DSNU₁₂₈₈ 10.44 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 100

40.0 dB

6.6 bit

1/SNR_{max} 1.00 %

PRNU₁₂₈₈ 4.19 %

Nonlinearity

LE 0.35%

LE_{min} -0.32%

LE_{max} 0.39%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 19.13 p

0.467 p/ μ m²

$\mu_{p,\text{sat}}$ 24057 p

587 p/ μ m²

$\mu_{e,\text{min}}$ 7.97 e⁻

0.194 e⁻/ μ m²

$\mu_{e,\text{sat}}$ 10018 e⁻

245 e⁻/ μ m²

Dynamic range

DR 1258

62.0 dB

10.3 bit

Dark current

$\mu_{c,\text{mean}}$ 101.7 DN/s

$\mu_{c,\text{mean}}$ 303.2 e⁻/s

$\mu_{c,\text{var}}$ 132.3 e⁻/s