

### Overview

- 1 mm
- PNP make function (NO)
- cable, 2 m
- -25 ... 75 °C
- IP 67



Picture similar



### Technical data

#### General data

Mounting type	Flush
Nominal sensing distance S <sub>n</sub>	1 mm
Hysteresis	2 ... 20 % of S <sub>r</sub>
Output indicator	LED red (backside)

#### Electrical data

Switching frequency	5 kHz
Voltage supply range +V <sub>s</sub>	6 ... 30 VDC
Current consumption max. (no load)	12 mA
Output circuit	PNP make function (NO)
Voltage drop V <sub>d</sub>	< 2 VDC
Output current	< 200 mA

#### Electrical data

Short circuit protection	Yes
Reverse polarity protection	Yes

#### Mechanical data

Type	Rectangular
Material (sensing face)	LCP
Housing material	Brass nickel plated
Dimension	6 mm
Housing length	20 mm
Connection types	Cable, L=2 m

#### Ambient conditions

Operating temperature	-25 ... +75 °C
Protection class	IP 67

### Remarks


- Short compact housing
- PUR cable

# IFFM 06P15A3/O1L

Inductive proximity switch - subminiature

Article number: 10146218

## Dimension drawing



## Connection diagram

