

OBDM 12P6910/S35A

Difference sensors

Article number: 10158748

Overview

- step analysis
- 16 ... 120 mm
- pulsed red laser diode
- PNP
- Teach-in
- connector M8 4 pin
- 50 °C
- IP 67




Picture similar



Technical data


General data		Electrical data	
Type	Step analysis	Output current	< 100 mA
Sensing distance Tw	16 ... 120 mm	Output pulse length	10 ms
Teach-in range min.	> 0.2 mm	Voltage drop Vd	< 2.8 VDC
Adjustment	Teach-in	Reverse polarity protection	Yes, Vs to GND
Power on indication	LED green	Short circuit protection	Yes
Output indicator	LED red	Mechanical data	
Light source	Pulsed red laser diode	Width / diameter	12.4 mm
Laser class	2	Height / length	37 mm
Wave length	650 nm	Depth	34.5 mm
Beam diameter	0.5 ... 0.2 mm	Type	Rectangular
Electrical data		Front (optics)	Glass
Response time	< 5 ms	Housing material	Die-cast zinc
Voltage supply range +Vs	12 ... 28 VDC	Connection types	Connector M8 4 pin
Current consumption max. (no load)	80 mA	Ambient conditions	
Current consumption typ.	40 mA	Operating temperature	0 ... +50 °C
Output circuit	PNP	Protection class	IP 67

Dimension drawing



- * emitter axis

Laser warning



LASER RADIATION
DO NOT STARE INTO BEAM

Wavelength: 640...670nm

IEC 60825-1, Ed. 3, 2014
CLASS 2 LASER PRODUCT

IEC 60825-1/2014 Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019

Connection diagram

