

LXG-200M

Dual GigE, 20 Megapixel, Monochrome

Article number: 11117848

Overview

- 5120 × 3840 px
- ams (CMOSIS) CMV20000
- 35 mm CMOS
- 12 fps
- Dual Gigabit Ethernet



Picture similar



GEN<i>i</i>CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV20000
Mono/Color	Mono
Sensor type	35 mm CMOS
Shutter type	Global shutter
Resolution	5120 × 3840 px
Pixel size	6.4 × 6.4 μm
Exposure time	0.1 ... 1000 ms

Data quality (EMVA 1288 typical)

Dark noise	9.45 e-
Saturation capacity	16150 e-
Dynamic range	64.1 dB
Signal-to-noise ratio	42.1 dB
Quantum efficiency	69.4 % @ 536 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 5120 × 3840 px, max. 12 fps Binning 2×2, 2560 × 1920 px, max. 12 fps Binning 1×2, 5120 × 1920 px, max. 12 fps Binning 2×1, 2560 × 3840 px, max. 12 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 5120 × 3840 px, max. 32 fps
Pixel formats	Mono8 Mono12 Mono12 Packed

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 255 LSB 12 Bit)
-----------------	---

Color models	Mono
--------------	------

Camera features

Synchronization	free running trigger
-----------------	-------------------------

Trigger sources	Hardware Software ActionCommand
-----------------	---------------------------------------

Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
---------------	--

Sequencer	Automated control for series of images using different sets of parameters
-----------	---

Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
---------------------	--

Digital inputs	1 input line
----------------	--------------

Digital outputs	3 output lines
-----------------	----------------

Internal image buffer	512 MB
-----------------------	--------

Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mb/s/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
----------------	---

Process interface	M8 / 8 pins
-------------------	-------------

Power supply	via M8 / 8 pins
--------------	-----------------

LXG-200M

Dual GigE, 20 Megapixel, Monochrome

Article number: 11117848

Technical data

Mechanical data

Lens mount	M58-mount (F-mount, M42, C-mount via adapter)
Width	60 mm
Height	60 mm
Depth	54.25 mm
Weight	≤ 290 g (M58-mount)
Material	housing: aluminum

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	Approx. 6.5 W @ 24 VDC Approx. 6.5 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +65 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Conformity

Conformity	CE RoHS KC (MSIP-REI-BkR-LXG-200M) EAC
------------	---

Dimension drawing

