

LXG-20M

Dual GigE, 2 Megapixel, Monochrome

Article number: 11137903

Overview

- 2048 × 1088 px
- ams (CMOSIS) CMV2000 V3
- 2/3" CMOS
- 111 fps
- Dual Gigabit Ethernet



Picture similar



GEN*i*CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV2000 V3
Mono/Color	Mono
Sensor type	2/3" CMOS
Shutter type	Global shutter
Resolution	2048 × 1088 px
Pixel size	5.5 × 5.5 μm
Exposure time	0.03 ... 1000 ms

Data quality (EMVA 1288 typical)

Dark noise	15.7 e-
Saturation capacity	10074 e-
Dynamic range	55.7 dB
Signal-to-noise ratio	40 dB
Quantum efficiency	48.6 % @ 536 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 2048 × 1088 px, max. 111 fps Binning 2×2, 1024 × 544 px, max. 336 fps Binning 1×2, 2048 × 544 px, max. 222 fps Binning 2×1, 1024 × 1088 px, max. 153 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 2048 × 1088 px, max. 337 fps
Pixel formats	Mono8 Mono10 Mono10 Packed

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 63 LSB 10 Bit)
-----------------	--

Color models	Mono
--------------	------

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB

Interfaces and connectors

Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mbits/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

LXG-20M

Dual GigE, 2 Megapixel, Monochrome

Article number: 11137903

Technical data

Mechanical data

Lens mount	C-mount
Width	60 mm
Height	60 mm
Depth	52.4 mm
Weight	≤ 340 g
Material	housing: aluminum

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	Approx. 6.2 W @ 24 VDC Approx. 5.2 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +64 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Conformity

Conformity	CE RoHS EAC
------------	-------------------

Dimension drawing

