




EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at www.standard1288.org and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 7, 21.08.2018, SN 0018(AEON).

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.

Vendor	Baumer
Model	VCXG.2-57M
Serial number	700009218540
Sensor diagonal	8.78 mm
Lens category	C-Mount
Resolution	2464 × 2048, 12 bit
Pixel size (h×v)	2.74 μm × 2.74 μm
Sensor	Sony IMX548
Sensor type	CMOS
Shutter type	Global shutter
Overlap cap.	Overlapped
Max. frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	533.3 nm
Wavelength FWHM	30.3 nm
Gain, black-level	1.0 / 40.0
Optional data measured	
None	






Summary Sheet for Operation Point 1 at a Wavelength of 533 nm

Type of data	Single	Gain, black-level	1.0 / 40.0
Exposure control	By irradiance	Environmental temperature	25.2°C
Exposure time	801.00 μ s	Camera body temperature	36.5°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono12	Wavelength, centr., FWHM	533 nm, 30.3 nm


Photon Transfer

Photon transfer mACC300053, 533 nm, 16.03.2023



Signal-to-Noise Ratio

SNR mACC300053, 533 nm, 16.03.2023



Quantum efficiency

η 69.2%

Overall system gain

K 0.409 DN/e⁻

$1/K$ 2.442 e⁻/DN

Temporal dark noise

σ_d 2.53 e⁻

$\sigma_{y,\text{dark}}$ 1.08 DN

Signal-to-noise ratio

SNR_{max} 98

39.8 dB

6.6 bit

$1/\text{SNR}_{\text{max}}$ 1.02 %

Absolute sensitivity threshold

$\mu_{p,\text{min}}$ 4.59 p

$\mu_{p,\text{min,area}}$ 0.611 p/ μm^2

$\mu_{e,\text{min}}$ 3.17 e⁻

$\mu_{e,\text{min,area}}$ 0.423 e⁻/ μm^2

Saturation capacity

$\mu_{p,\text{sat}}$ 13828 p

$\mu_{p,\text{sat,area}}$ 1842 p/ μm^2

$\mu_{e,\text{sat}}$ 9569 e⁻

$\mu_{e,\text{sat,area}}$ 1275 e⁻/ μm^2

Dynamic range

DR 3014

69.6 dB

11.6 bit

Spatial nonuniformities

DSNU₁₂₈₈ 0.49 e⁻

0.20 DN

PRNU₁₂₈₈ 0.39 %

Linearity error

LE_{min} -0.35%

LE_{max} 0.83%

Dark current

$\mu_{c,\text{mean}}$ 0 \pm 0 e⁻/s

0.0 DN/s

$\mu_{c,\text{var}}$ 24 \pm 1 e⁻/s

T_d — °C