

产品一览

- Outstanding reliability and unrivalled immunity against ambient light
- Focused laser beam for small objects or gaps
- qTeach - tamper-proof, simple teach-in with ferromagnetic tool
- Quick mounting by means of M3 threaded bushes made of stainless steel



图片与实际产品类似



技术数据

基本参数

类型	背景抑制型
感应距离 Tw	20 ... 120 mm
感应范围 Tb	3 ... 132 mm
Smallest object recognizable typ.	0,05 mm (距离40 mm)
上电指示灯	绿色LED
调节/镜头受污指示灯	闪烁的输出指示灯
输出指示灯	黄色LED
感应距离调节	qTeach
焦距	40 mm
交互影响抑制	是
光束类型	点激光
光轴校准	< 1.5°

光源

光源	脉冲红色激光二极管
激光等级	1
波长	680 nm

电气参数

响应时间 / 释放时间	≤ 0,5 ms
Jitter	≤ 0,12 ms
电源电压范围 +Vs	10 ... 30 VDC

电气参数

最大电流消耗 (无负载)	20 mA (@ 10 VDC)
典型电流消耗	10 mA (@ 24 VDC)
压降 Vd	< 2 VDC
输出功能	亮通/暗通
输出电路	NPN互补
输出电流	50 mA
短路保护	是
反极性保护	是

机械参数

宽度 / 直径	8 mm
高度 / 长度	25,1 mm
深度	15,8 mm
类型	矩形
Mechanical mounting	M3 螺纹套筒 (不锈钢)
外壳材质	塑料 (ASA、PMMA)
前端光学元件	PMMA
连接方式	M8 引线接头 · 4针 · L=200 mm
Cable characteristics	PVC / PVC 4 x 0,08 mm ²

环境条件


防护等级	IP 67
工作温度	-20 ... +50 °C

O200.GL-NV1T.72NV/F040_H006


Diffuse sensors with background suppression - miniature

Article number: 11231143

尺寸图



典型光束特性




激光报警

**CLASS 1 LASER
PRODUCT**


IEC 60825-1/2014

Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3., as described in Laser Notice No. 56, dated May 8, 2019


接线图



针脚定义



感应距离示意图



迟滞曲线

