

**Overview**

- light barrier
- 60 ... 600 mm
- pulsed PinPoint LED
- push-pull
- Teach-in and IO-Link
- flylead connector M12, L=300 mm
- -25 ... 60 °C
- IP 68/69K & proTect+



Picture similar



**Technical data**

**General data**

Type	Light barrier
Special type	Hygienic design
Version	Standard object detection
Background position Sde	60 ... 600 mm
Scanning range Sa	90% ... 85% Sde
Power on indication	LED green
Light indicator	LED yellow
Sensing distance adjustment	Teach-in and IO-Link
Suppression of reciprocal influence	Yes
Alignment optical axis	< 1°
Approvals/certificates	Ecolab Adapted from EHEDG

**Light Source**

Light source	Pulsed PinPoint LED
Wave length	630 nm

**Electrical data**

Response time / release time	< 0.49 ms
Voltage supply range +Vs	10 ... 30 VDC

**Electrical data**

Current consumption max. (no load)	40 mA
Current consumption typ.	30 mA
Voltage drop Vd	<3 VDC
Output function	Light / dark operate
Output circuit	Push-pull
Output current	100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

**Mechanical data**

Width / diameter	20.2 mm
Height / length	47.7 mm
Depth	36.4 mm
Design	Rectangular
Housing material	Stainless steel 1.4404 (V4A)
Front (optics)	PMMA
Connection types	Flylead connector M12, L=300 mm

**Ambient conditions**

Protection class	IP 68/69K & proTect+
Operating temperature	-25 ... +60 °C

**Remarks**


- Magnetic Teach
- IO-Link: V1.1, filter functions, qTeach lock adjustable

# O500H.SP-GW1J.PVOK

SmartReflect Light barriers - hygiene


Article number: 11125107

## Dimension drawing




- Cable length L = 300 mm

## Connection diagram



## Pin assignment



## Beam characteristic (typically)

