

Vue d'ensemble

- M8, male, A-coded, 3-poles; PUR, 200 cm; M8, female, A-coded, 3-poles
- Dragchain capable; suitable for robotics $\pm 180^\circ/\text{m}$
- Head A: IP65, IP66K, IP67; Head B: IP65, IP66K, IP67
- Cable: good resistance against chemicals, flames, oils


Caractéristiques techniques

| Side A | | Cable | |
|------------------------------|---------------------------------------|------------------------------------|--------------------------|
| Head A: Connection | M8 | Cable: Temperature range (mobile) | - 25 ...+ 80 °C |
| Head A: Angle cable outlet | 0° | Cable: Temperature range (fixed) | - 40 ...+ 80 °C |
| Head A: Gender | Male | Operating voltage (only UL listed) | 30 V AC/DC |
| Head A: Coding | A | Shielded | No |
| Head A: No. of poles | 3 | Bending radius (fixed) | 20,5 mm |
| Head A: LED | No | Number of wires | 3 |
| Head A: Width across flats | AF9 | Number and diameter of wires | 3x0,25 |
| Head A: Tightening torque | 0,4 Nm | Length tolerance | + 10 cm |
| Head A: Knurled nut material | Brass, surface Ni | Cable length | 200 cm |
| Head A: Body color | Black | Acceleration (C-track) | max. 10 m/s ² |
| Labeling sleeve side A | Yes | AWG | 24 |
| Side B | | Bending radius (fixed) | min. 5 × outer diameter |
| Head B: Connection | M8 | Torsion speed | max. 35 cycles/min |
| Head B: Angle cable outlet | 0° | Bending radius (mobile) | min. 10 × outer diameter |
| Head B: Gender | Female | Cable type | 3 |
| Head B: Coding | A | Cable weight | approx. 26,4 g/m |
| Head B: No. of poles | 3 | Conductor structure | 32 × 0,1 mm |
| Head B: LED | Oui | Cable diameter | 4,1 mm ± 5% |
| Head B: LED switching status | PNP | Conductor: Material | Copper, bare |
| Head B: Width across flats | AF9 | External sheath: Material | PUR |
| Head B: Tightening torque | 0,4 Nm | Insulation: Material | PP |
| Head B: Knurled nut material | Zinc-pressure die casting, surface Ni | No. of bending cycles (C-track) | approx. 10000000 Cycles |
| Head B: Body color | Transparent | Nominal voltage | 300 V |
| Head B: Gasket material | FKM | No. of torsion cycles | approx. 2000000 Cycles |
| Labeling sleeve side B | Yes | Paired stranding | No |
| Cables | | Single wire diameter | 0,1 mm |
| Cable length | 200 cm | Cable: Test voltage | 2,5 kV |
| Length tolerance | + 10 cm | Torsion stress in ° | $\pm 180^\circ/\text{m}$ |
| Shielded | No | Total stranding | 3 wires strand |
| Conductor structure | 32 × 0,1 mm | Travel speed (C-track) | max. 3 m/s |
| AWG | 24 | Traversing path (horizontal) | max. 10 m |
| External sheath: Material | PUR | Wire cross section | 0,25 mm ² |
| External sheath: Color | Black | Wire processing | No |
| Cable diameter | 4,1 mm ± 5% | Wire diameter incl. isolation | 1,25 mm ± 5% |
| Wire cross section | 0,25 mm ² | External sheath: Color | Black |

Caractéristiques techniques

Données électriques

| | |
|------------------------------------|--------------------|
| Operating voltage | 24 V DC \pm 25 % |
| Operating voltage (only UL listed) | 30 V AC/DC |
| Nominal voltage | 300 V |
| Contact resistance | max. 30 mOhm |
| Operating current per contact | max. 4 A |

Données mécaniques

| | |
|---------------------------------|---------------------------------|
| Head A: Degree of protection | IP65, IP66K, IP67 |
| Head B: Degree of protection | IP65, IP66K, IP67 |
| Bending radius (mobile) | min. 10 \times outer diameter |
| Bending radius (fixed) | min. 5 \times outer diameter |
| No. of bending cycles (C-track) | approx. 10000000 Cycles |
| Torsion speed | max. 35 cycles/min |
| Torsion stress in $^{\circ}$ | \pm 180 $^{\circ}$ /m |
| No. of torsion cycles | approx. 2000000 Cycles |
| Acceleration (C-track) | max. 10 m/s ² |
| Travel speed (C-track) | max. 3 m/s |

Conditions ambiantes

| | |
|----------------------------|----------------------------|
| Temperature range (mobile) | - 25 ... + 80 $^{\circ}$ C |
| Temperature range (fixed) | - 25 ... + 80 $^{\circ}$ C |

Conditions ambiantes

| | |
|-----------------------------------|---|
| Cable: Temperature range (fixed) | - 40 ... + 80 $^{\circ}$ C |
| Dragchain capable | Oui |
| Head A: Chemical resistance | No |
| Head A: Flame resistance | HB (UL 94) |
| Head A: Oil resistance | ASTM 1 oil, mineral oils, limited to hydraulic oils |
| Head A: Acid and alkali resistant | No |
| Head A: Pollution degree | 3 |
| Head B: Chemical resistance | No |
| Head B: Flame resistance | HB (UL 94) |
| Head B: Oil resistance | ASTM 1 oil, mineral oils, limited to hydraulic oils |
| Head B: Acid and alkali resistant | No |
| Head B: Pollution degree | 3 |
| Cable: Chemical resistance | Good (DIN EN 60811-404) |
| Cable: Flame resistance | Conform UL 1581 §1090 (H), CSA FT2, IEC 60332-2-2 |
| Cable: Oil resistance | Good (DIN EN 60811-404) |
| Cable: Silicone-free | Oui |

Commercial data

| | |
|--------|----------|
| Eclass | 27060311 |
|--------|----------|

Side A

Technical drawing



Side A

Coding



Side B

Technical drawing



Dessin d'encombrement



Coding



Schéma de raccordement

