

**Overview**

- Computer lens
- 16 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount
- suitable for visible and SWIR wavelengths (400 - 1700 nm)



*Picture similar*

Technical data	
<b>General data</b>	
Manufacturer	Computar
<b>Mechanical data</b>	
Lens mount	C-mount
Dimensions	33,5 mm × 28,2 mm
Max. outer diameter	33.5 mm
Max. length (excl. thread)	28.2 mm
Weight	≤ 60 g
Filter thread	M 30,5 × 0,5
<b>Lens data</b>	
Lens resolution	1.3 MP
Pixel resolution	5 µm
<b>Lens data</b>	
Focal length	16 mm
Format	2/3"
Aperture	F1.4-16
Aperture control	Manual
M.O.D.	0.3 m
Horizontal angle of view	30.8 °
Vertical angle of view	23.4 °
Diagonal angle of view	38.0 °
At image format	8,8 mm × 6,6 mm
<b>Environmental conditions</b>	
Operating temperature	-10 ... +50 °C