

Overview

- M12, male, A-coded, 5-poles; PUR, 2500 cm; M12, female, 90°, A-coded, 5-poles
- Dragchain capable, suitable for robotics $\pm 180^\circ/\text{m}$
- Head A: IP65, IP66K, IP67
- Cable: good resistance against chemicals, flames and oils
- Halogen free



Technical data

Side A		Cable	
Head A: Connection	M12	Shielded	No
Head A: Angle cable outlet	0°	Cable length	2500 cm
Head A: Gender	Male	AWG	22
Head A: Coding	A	Torsion speed	max. 35 cycles/min
Head A: No. of poles	5	Cable type	3
Head A: LED	No	Conductor: Material	Copper, bare
Head A: Width across flats	AF13	External sheath: Material	PUR
Head A: Knurled nut material	Zinc-pressure die casting, surface Ni	Insulation: Material	PP
Head A: Body color	Black	Paired stranding	No
Labeling sleeve side A	Yes	Torsion stress in °	$\pm 180^\circ/\text{m}$
Side B		Total stranding	5 wires strand around core-filler
Head B: Connection	M12	Wire cross section	0.34 mm ²
Head B: Angle cable outlet	90°	Wire processing	No
Head B: Gender	Female	External sheath: Color	Black
Head B: Coding	A	Mechanical data	
Head B: No. of poles	5	Head A: Degree of protection	IP65, IP66K, IP67
Head B: LED	No	Head B: Degree of protection	IP65, IP66K, IP67
Head B: Width across flats	AF13	Torsion speed	max. 35 cycles/min
Head B: Knurled nut material	Zinc-pressure die casting, surface Ni	Torsion stress in °	$\pm 180^\circ/\text{m}$
Head B: Body color	Black	Environmental conditions	
Head B: Gasket material	FKM	Dragchain capable	Yes
Labeling sleeve side B	Yes	Head A: Chemical resistance	No
Cables		Head A: Flame resistance	HB (UL 94)
Cable length	2500 cm	Head A: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.
Shielded	No		
AWG	22		
External sheath: Material	PUR		
External sheath: Color	Black		
Wire cross section	0.34 mm ²		

Technical data
Environmental conditions

Head A: Acid and alkali resistant	No
Head A: Pollution degree	3
Head B: Chemical resistance	No
Head B: Flame resistance	HB (UL 94)
Head B: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.

Environmental conditions

Head B: Acid and alkali resistant	No
Head B: Pollution degree	3
Cable: Chemical resistance	Good (DIN EN 60811-404)
Cable: Flame resistance	Conform UL 1581 §1090 (H)
Cable: Oil resistance	Good (DIN EN 60811-404)
Cable: Silicone-free	Yes

Commercial data

Eclass	27060311
--------	----------