

**Vue d'ensemble**

- M12, male, A-coded, 5-poles; PUR, 500 cm; M12, female, 90°, A-coded, 5-poles
- Dragchain capable, suitable for robotics  $\pm 180$  °/m
- Head A: IP65, IP66K, IP67
- Cable: good resistance against chemicals, flames and oils
- Halogen free


**Caractéristiques techniques**
**Side A**

Head A: Connection	M12
Head A: Angle cable outlet	0°
Head A: Gender	Male
Head A: Coding	A
Head A: No. of poles	5
Head A: LED	No
Head A: Width across flats	AF13
Head A: Tightening torque	0,6 Nm
Head A: Knurled nut material	Zinc-pressure die casting, surface Ni
Head A: Body color	Black
Labeling sleeve side A	Yes

**Side B**

Head B: Connection	M12
Head B: Angle cable outlet	90°
Head B: Gender	Female
Head B: Coding	A
Head B: No. of poles	5
Head B: LED	No
Head B: Width across flats	AF13
Head B: Knurled nut material	Zinc-pressure die casting, surface Ni
Head B: Body color	Black
Head B: Gasket material	FKM
Labeling sleeve side B	Yes

**Cables**

Cable length	500 cm
Shielded	No
AWG	22
External sheath: Material	PUR
External sheath: Color	Black

**Cables**

Wire cross section	0,34 mm <sup>2</sup>
--------------------	----------------------

**Cable**

Shielded	No
Cable length	500 cm
AWG	22
Torsion speed	max. 35 cycles/min
Cable type	3
Conductor: Material	Copper, bare
External sheath: Material	PUR
Insulation: Material	PP
Paired stranding	No
Torsion stress in °	$\pm 180$ °/m
Total stranding	5 wires strand around core-filler
Wire cross section	0,34 mm <sup>2</sup>
Wire processing	No
External sheath: Color	Black

**Données mécaniques**

Head A: Degree of protection	IP65, IP66K, IP67
Head B: Degree of protection	IP65, IP66K, IP67
Torsion speed	max. 35 cycles/min
Torsion stress in °	$\pm 180$ °/m

**Conditions ambiantes**

Dragchain capable	Oui
Head A: Chemical resistance	No
Head A: Flame resistance	HB (UL 94)

**Caractéristiques techniques**
**Conditions ambiantes**

Head A: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.
Head A: Acid and alkali resistant	No
Head A: Pollution degree	3
Head B: Chemical resistance	No
Head B: Flame resistance	HB (UL 94)
Head B: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.

**Conditions ambiantes**

Head B: Acid and alkali resistant	No
Head B: Pollution degree	3
Cable: Chemical resistance	Good (DIN EN 60811-404)
Cable: Flame resistance	Conform UL 1581 §1090 (H)
Cable: Oil resistance	Good (DIN EN 60811-404)
Cable: Silicone-free	Oui

**Commercial data**

Eclass	27060311
--------	----------